

# Product data sheet

## Characteristics

# 56DOL9/4B-GY

## 56DOL9/4B STRTR DOL 3PH 4KW



### Main

Range of product	Series 56
------------------	-----------

### Complementary

Colour code	GY
Motor starter type	Direct on line
[Us] rated supply voltage	415 V AC 50 Hz
Network type	AC
Rated operational power in W	4 kW at 400 V (AC-3)
[Ie] rated operational current	9 A
Overload current	2.5...4 A
Network number of phases	3 phases
Product destination	2 push-button




### Environment

Ambient air temperature for operation	-20...60 °C
---------------------------------------	-------------

### Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Weight	1.4 kg

### Offer Sustainability

REACH Regulation	 <a href="#">REACH Declaration</a>
EU RoHS Directive	Compliant with Exemptions
China RoHS Regulation	 <a href="#">China RoHS Declaration</a>
RoHS exemption information	 Yes
WEEE	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins