



### Main

Range of product	Series 56
------------------	-----------

### Complementary

Colour code	GY
Motor starter type	Direct on line
[Us] rated supply voltage	415 V AC 50 Hz
Network type	AC
Rated operational power in W	4 kW at 400 V (AC-3)
[Ie] rated operational current	9 A
Overload current	2.5...4 A
Network number of phases	3 phases
Product destination	2 push-button

### Environment

Ambient air temperature for operation	-20...60 °C
---------------------------------------	-------------

### Packing Units

Package 1 Weight	0.001 kg
------------------	----------

### Offer Sustainability

Sustainable offer status	Green Premium product
EU RoHS Directive	Compliant <a href="#">EU RoHS Declaration</a>
Mercury free	Yes
RoHS exemption information	<a href="#">Yes</a>
China RoHS Regulation	<a href="#">China RoHS Declaration</a>
Environmental Disclosure	<a href="#">Product Environmental Profile</a>
WEEE	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins