

Product data sheet

Characteristics

56DOL9/6-RO

56 Series - Direct Online Starter - 3 Phase - 4kW - 240V - orange



Main

Range of product	Series 56
Product or component type	Switch
Colour	Cover: orange

Complementary

Colour code	RO
Motor starter type	Direct on line
Control type	Push-button
[Us] rated supply voltage	240 V AC 50 Hz
Network type	AC
Rated operational power in W	4 kW at 240 V (AC-3)
[Ie] rated operational current	9 A
Overload current	4...6 A
Connections - terminals	Screw terminal solid Screw terminal stranded
Tightening torque	0.8 N.m
Network number of phases	3 phases
Product destination	2 push-button
Height	204 mm
Width	101 mm
Net weight	1.4 kg
Targeted country	Australia
Market segment	Small commercial Industry Utility

Environment

Suitability for isolation	No
IP degree of protection	IP66 conforming to AS 60529
Ambient air temperature for operation	-25...75 °C
Standards	AS/NZS 3133 AS/NZS 3100

Packing Units

Package 1 Weight	1.400 kg
------------------	----------

Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	REACH Declaration
EU RoHS Directive	Compliant EU RoHS Declaration
Mercury free	Yes
RoHS exemption information	Yes
China RoHS Regulation	China RoHS Declaration
Environmental Disclosure	Product Environmental Profile