

Product data sheet

Characteristics

56E16-GY

56 Series Enclosure - 16 Gang - 4 x 32mm - 4 x 40mm conduit entries



Main

Range	Clipsal - 56 Series
Product or component type	Industrial box
Colour	Grey (RAL 7035)

Complementary

Device mounting	Surface
Mounting mode	Wall mount
Material	PVC (polyvinyl chloride): housing
Length	396 mm
Width	396 mm
Depth	63 mm
Net weight	2.94 kg
IP degree of protection	IP66 conforming to AS 60529
Standards	AS 3100


Environment

Ambient air temperature for operation	-25...75 °C
---------------------------------------	-------------

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Weight	2383.25 g
Package 1 Height	6.6 cm
Package 1 width	40 cm
Package 1 Length	40.4 cm
Unit Type of Package 2	CAR
Number of Units in Package 2	5
Package 2 Weight	10500.0 g
Package 2 Height	42.5 cm
Package 2 width	33.5 cm
Package 2 Length	46 cm

Offer Sustainability

EU RoHS Directive	Pro-active compliance (Product out of EU RoHS legal scope)  EU RoHS Declaration
-------------------	--