

Product data sheet

Characteristics

56ES2-GY

Clipsal - 56 Series, Mounting Back Box,
Shallow, 2 Gang, 38x101x198mm



Main

Range of product	Series 56
Range	Clipsal - 56 Series
Product brand	Clipsal
Product or component type	Enclosure
Colour	Grey (RAL 7035)

Complementary

Number of gangs	2 gangs
Shape	Rectangular
Device mounting	Surface
Mounting mode	Wall-mounted
Cable entry number	3
Material	PVC (polyvinyl chloride): housing
Number of mounting holes	4
Length	38 mm
Width	102 mm
Depth	40 mm
Height	198 mm
Net weight	0.34 kg
IP degree of protection	IP66 conforming to AS 60529
Standards	AS 3100



Environment

Ambient air temperature for operation	-25...75 °C
---------------------------------------	-------------

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	3.8 cm
Package 1 Width	10.2 cm
Package 1 Length	19.8 cm
Package 1 Weight	306 g

Offer Sustainability

REACH Regulation	 REACH Declaration
EU RoHS Directive	Pro-active compliance (Product out of EU RoHS legal scope)
Mercury free	Yes
China RoHS Regulation	 China RoHS Declaration
RoHS exemption information	 Yes