

## Product data sheet

### Characteristics

# 56EV2/225-GY

56 Series Enclosure - 2 Gang - Vertical - 2 x  
25mm conduit entries



### Main

Range of product	Series 56
Range	Clipsal - 56 Series
Product brand	Clipsal
Colour	Grey (RAL 7035)

### Complementary

Number of gangs	2 gangs
Device mounting	Surface
Mounting mode	Wall-mounted
Cable entry number	2
Material	PVC (polyvinyl chloride): housing
Length	104 mm
Width	145 mm
Depth	110 mm
Height	110 mm
Net weight	0.707 kg
IP degree of protection	IP66 conforming to AS 60529
Standards	AS 3100

### Environment

Ambient air temperature for operation	-25...75 °C
---------------------------------------	-------------

### Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Weight	672.5 g
Package 1 Height	12 cm
Package 1 width	11 cm
Package 1 Length	21 cm
Unit Type of Package 2	CAR
Number of Units in Package 2	12
Package 2 Weight	8.49 kg
Package 2 Height	25.4 cm
Package 2 width	34.8 cm
Package 2 Length	44.5 cm

## Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	<a href="#">REACH Declaration</a>
EU RoHS Directive	Compliant <a href="#">EU RoHS Declaration</a>
Mercury free	Yes
RoHS exemption information	<a href="#">Yes</a>
China RoHS Regulation	<a href="#">China RoHS Declaration</a>
Environmental Disclosure	<a href="#">Product Environmental Profile</a>