

Product data sheet

Characteristics

56EV2/32-GY

56 Series Enclosure - 2 Gang - Vertical - 1 x
32mm conduit entry



Main

Range of product	Series 56
Range	Clipsal - 56 Series
Product brand	Clipsal
Colour	Grey (RAL 7035)

Complementary

Number of gangs	2 gangs
Device mounting	Surface
Mounting mode	Wall-mounted
Cable entry number	1
Material	PVC (polyvinyl chloride): housing
Length	104 mm
Width	145 mm
Depth	110 mm
Height	110 mm
Net weight	0.707 kg
IP degree of protection	IP66 conforming to AS 60529
Standards	AS 3100

Environment

Ambient air temperature for operation	-25...75 °C
---------------------------------------	-------------

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Weight	670.5 g
Package 1 Height	12 cm
Package 1 width	11 cm
Package 1 Length	21 cm
Unit Type of Package 2	CAR
Number of Units in Package 2	12
Package 2 Weight	8.47 kg
Package 2 Height	25.4 cm
Package 2 width	34.8 cm
Package 2 Length	44.5 cm

Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	REACH Declaration
EU RoHS Directive	Compliant EU RoHS Declaration
Mercury free	Yes
RoHS exemption information	Yes
China RoHS Regulation	China RoHS Declaration
Environmental Disclosure	Product Environmental Profile