

Product data sheet

Characteristics

56HPG2/2-CM

56 Series High Pressure Gasket - 2 x1 Gang



Main

Range	Clipsal - 56 Series
Product brand	Clipsal
Product or component type	Gasket
Accessory / separate part category	Mounting accessory

Complementary

Colour	Cream
Net weight	0.06 kg

Environment

IP degree of protection	IP66 conforming to AS 60529
Ambient air temperature for operation	-25...75 °C

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Weight	47.0 g
Package 1 Height	1.5 cm
Package 1 width	10.8 cm
Package 1 Length	20 cm
Unit Type of Package 2	BB1
Number of Units in Package 2	5
Package 2 Weight	0.286 kg
Package 2 Height	12.6 cm
Package 2 width	7 cm
Package 2 Length	25.4 cm
Unit Type of Package 3	CAR
Number of Units in Package 3	50
Package 3 Weight	3.4 kg
Package 3 Height	26.5 cm
Package 3 width	24.6 cm
Package 3 Length	40.2 cm

The information provided in this documentation contains general descriptions and/or technical characteristics of the performance of the products contained herein. This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications. It is the duty of any such user or integrator to perform the appropriate and complete risk analysis, evaluation and testing of the products with respect to the relevant specific application or use thereof. Neither Schneider Electric Industries SAS nor any of its affiliates or subsidiaries shall be responsible or liable for misuse of the information contained herein.

Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	REACH Declaration
EU RoHS Directive	Compliant EU RoHS Declaration
Mercury free	Yes
RoHS exemption information	Yes
China RoHS Regulation	China RoHS Declaration
Environmental Disclosure	Product Environmental Profile