

Product data sheet

Characteristics

56K1CV310-GY

Clipsal - 56 Series, Keyed Three PIN Socket, 10A, 250V. Temperature range -25C to +75C



Main

Range of product	Series 56
Range	Clipsal - 56 Series
Product brand	Clipsal
Product or component type	Switched socket
Device application	Power supply
Colour	Grey
Outlet standard deviation	Australian/New Zealand

Complementary

Plug, socket category	Low voltage
Plug, socket, control station shape	Straight Angled
Mounting mode	Surface mounting
[In] rated current	10 A
[Ue] rated operational voltage	250 V AC 50 Hz conforming to EN 60309-2
Poles description	1P + N + E
Voltage colour	Blue
Protection type	Without protection
Duration	6 h
Material	Polycarbonate: cover
Contacts material	Pins: phosphor bronze
Connections - terminals	Screw terminals 1.5...6 mm ²
Depth	85 mm
Width	101 mm
Height	204 mm
Targeted country	Australia

Environment

IP degree of protection	IP66 conforming to AS 60529
Ambient air temperature for operation	-25...75 °C
Standards	AS/NZS 3112 AS/NZS 4417.1

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	8.85 cm
Package 1 Width	10.35 cm
Package 1 Length	20.65 cm
Package 1 Weight	758.0 g

Unit Type of Package 2	CAR
Number of Units in Package 2	12
Package 2 Height	21.4 cm
Package 2 Width	29.7 cm
Package 2 Length	42.9 cm
Package 2 Weight	9.52 kg

Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	REACH Declaration
EU RoHS Directive	Compliant EU RoHS Declaration
Mercury free	Yes
China RoHS Regulation	China RoHS Declaration
RoHS exemption information	Yes
Environmental Disclosure	Product Environmental Profile