

## Product data sheet

### Characteristics

# 56K1SW310MSK-GY

## SURFACE SWITCH IP66 3 POLE 10A KEY OPERATED



### Main

Range of product	Series 56
Product brand	Clipsal
Device presentation	Basic element with full cover plate

### Complementary

Switch function	3-pole
Actuator	Key
Number of poles	3
Device mounting	Surface
Fixing mode	By screws
Material	PC (polycarbonate)
Local signalling	without
[Ue] rated operational voltage	500 V AC
Rated current	10 A
Marking	ON-OFF
Marking location	Marking on surface

### Environment

Standards	AS/NZS 3123 AS/NZS 3947-3
-----------	------------------------------

### Packing Units

Package 1 Weight	0.001 kg
------------------	----------

The information provided in this documentation contains general descriptions and/or technical characteristics of the performance of the products contained herein. This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications. It is the duty of any such user or integrator to perform the appropriate and complete risk analysis, evaluation and testing of the products with respect to the relevant specific application or use thereof. Neither Schneider Electric Industries SAS nor any of its affiliates or subsidiaries shall be responsible or liable for misuse of the information contained herein.