

## Product data sheet

### Characteristics

# 56K1SW310MSK-GY

## SURFACE SWITCH IP66 3 POLE 10A KEY OPERATED



### Main

Range of product	Series 56
Product brand	Clipsal
Device presentation	Basic element with full cover plate

### Complementary

Switch function	3-pole
[Icm] rated short-circuit making capacity	1 kA
Number of poles	3
Device mounting	Surface
Fixing mode	By screws
Material	PC (polycarbonate)
Local signalling	without
[Ue] rated operational voltage	500 V AC
Rated current	10 A
Marking	ON-OFF
Marking location	Marking on surface
Actuator	Key
[Icw] rated short-time withstand current	1.2 kA for 1 s
[Uimp] rated impulse withstand voltage	4 kV

### Environment

Standards	AS/NZS 3123 AS/NZS 3947-3
-----------	------------------------------

### Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Weight	590.0 g
Package 1 Height	11.25 cm
Package 1 width	10.35 cm
Package 1 Length	10.65 cm
Unit Type of Package 2	CAR
Number of Units in Package 2	24
Package 2 Weight	14.545 kg
Package 2 Height	21 cm
Package 2 width	34.8 cm
Package 2 Length	44.5 cm