

## Product data sheet

### Characteristics

# 56K2SW115CK-GY

Switch, Clipsal - 56 Series, 1 Pole, 250VAC, 15A, Common Key Lock, On/Off Locking Position



#### Main

Range of product	Series 56
Range	Clipsal - 56 Series
Product brand	Clipsal
Product or component type	Switch
Assembly Type	Basic element with full cover plate
Device application	Control
Handle colour	Grey
Suitability for isolation	No
Colour	Cover: grey

#### Complementary

Poles description	1P
Control type	Rotary knob
Number of poles	1
Installation Type	Surface
Material	PC (polycarbonate)
Tightening torque	0.8 N.m
Local signalling	without
[Ue] rated operational voltage	250 V AC 50 Hz
Rated current	15 A
Marking	ON-OFF
Marking location	Marking on surface
Mounting Type	By screws
Breaking capacity	15 kA
Targeted country	Australia
Height	107 mm
Width	101 mm
Depth	83 mm
Product weight	0.4 kg
Actuator	Key
Motor M-rating AS3133	M80 at 250 V
Switch function	1-pole
Rotary handle padlocking	2 padlocks 8 mm

#### Environment

Ambient air temperature for operation	-25...75 °C
IP degree of protection	IP66 conforming to AS 60529
Standards	AS/NZS 3133

## Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	11.2 cm
Package 1 Width	10.6 cm
Package 1 Length	10.6 cm
Package 1 Weight	411.0 g
Unit Type of Package 2	CAR
Number of Units in Package 2	24
Package 2 Height	21.0 cm
Package 2 Width	34.8 cm
Package 2 Length	44.5 cm
Package 2 Weight	10.008 kg

## Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	<a href="#">REACH Declaration</a>
EU RoHS Directive	Compliant with Exemptions
China RoHS Regulation	<a href="#">China RoHS Declaration</a>
RoHS exemption information	<a href="#">Yes</a>
Environmental Disclosure	<a href="#">Product Environmental Profile</a>
Circularity Profile	No need of specific recycling operations