

Product data sheet

Characteristics

56K2SW250-GY

Switches, Key Operated Surface Switches,
IP66, 500V 50A, Double Pole



Main

Range of product	Series 56
Product brand	Clipsal
Device presentation	Basic element with full cover plate

Complementary

Switch function	2-pole
Number of poles	2
Device mounting	Surface
Fixing mode	By screws
Material	PC (polycarbonate)
Local signalling	without
[Ue] rated operational voltage	500 V AC
Rated current	50 A
Marking	ON-OFF
Marking location	Marking on surface
Actuator	Key


Environment

Standards	AS/NZS 3123 AS/NZS 3947-3
-----------	------------------------------

Packing Units

Unit Type of Package 1	Db
Number of Units in Package 1	1
Package 1 Height	11.25 cm
Package 1 Width	11.25 cm
Package 1 Length	10.65 cm
Package 1 Weight	0.6 kg

Offer Sustainability

REACH Regulation	 REACH Declaration
EU RoHS Directive	Compliant  EU RoHS Declaration
Mercury free	Yes
China RoHS Regulation	 China RoHS Declaration
RoHS exemption information	 Yes