

## Product data sheet

### Characteristics

# 56K2SW310LE-GY

## 56 Series - Switch - Keylock - 3 Pole - 10A - 500V - Less Enclosure - grey



### Main

Range of product	Series 56
Range	Clipsal - 56 Series
Product brand	Clipsal
Product or component type	Switch
Device presentation	Basic element with full cover plate
Device application	Control
Colour	Cover: grey
Handle colour	Grey
Suitability for isolation	Yes

### Complementary

Switch function	3-pole
Poles description	3P
[Icm] rated short-circuit making capacity	1 kA
Control type	Rotary knob
Number of poles	3
Device mounting	Surface
Material	PC (polycarbonate)
Tightening torque	0.8 N.m
Local signalling	without
[Ue] rated operational voltage	500 V AC 50 Hz
Rated current	10 A
Marking	ON-OFF
Marking location	Marking on surface
Height	107 mm
Width	101 mm
Depth	76 mm
Net weight	0.36 kg
Breaking capacity	10 kA
Targeted country	Australia
Rotary handle padlocking	2 padlocks 8 mm
Actuator	Key
[Icw] rated short-time withstand current	1.2 kA for 1 s
[Uimp] rated impulse withstand voltage	4 kV
Motor M-rating AS3133	M200 at 500 V

### Environment

Ambient air temperature for operation	-25...75 °C
IP degree of protection	IP66 conforming to AS 60529
Standards	AS/NZS 3133

The information provided in this documentation contains general descriptions and/or technical characteristics of the performance of the products contained herein. This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications. It is the duty of any such user or integrator to perform the appropriate and complete risk analysis, evaluation and testing of the products with respect to the relevant specific application or use thereof. Neither Schneider Electric Industries SAS nor any of its affiliates or subsidiaries shall be responsible or liable for misuse of the information contained herein.

## Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Weight	325.65 g
Package 1 Height	9.95 cm
Package 1 width	9.95 cm
Package 1 Length	9.95 cm
Unit Type of Package 2	CAR
Number of Units in Package 2	24
Package 2 Weight	8.2 kg
Package 2 Height	21 cm
Package 2 width	34.8 cm
Package 2 Length	44.5 cm

## Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	<a href="#">REACH Declaration</a>
EU RoHS Directive	Compliant <a href="#">EU RoHS Declaration</a>
Mercury free	Yes
RoHS exemption information	<a href="#">Yes</a>
China RoHS Regulation	<a href="#">China RoHS Declaration</a>
Environmental Disclosure	<a href="#">Product Environmental Profile</a>