

## Product data sheet

### Characteristics

# 56M42-CG

## Clipsal - 56 Series, 40 Module Adaptor, 2 Aperture



### Main

Range of product	Series 56
Range	Clipsal - 56 Series
Product brand	Clipsal
Product or component type	Enclosure
Plug, socket category	Low voltage
Outlet standard	Industrial
Colour	Grey (RAL 7035)

### Complementary

Number of gangs	1 gang
Shape	Square
Device mounting	Surface
Cable entry number	3
Material	ABS (acrylonitrile butadiene-styrene): cover
Fixing mode	By screws
Tightening torque	0.8 N.m
Cable entry	3 entries of 25 mm diameter
Length	107 mm
Width	101 mm
Depth	77 mm
Height	107 mm
Net weight	0.5 kg
IP degree of protection	IP66
Targeted country	Australia




### Environment

Ambient air temperature for operation	-25...75 °C
---------------------------------------	-------------

### Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	11.28 cm
Package 1 Width	10.35 cm
Package 1 Length	10.65 cm
Package 1 Weight	0.5 kg

Offer Sustainability

REACH Regulation	 <a href="#">REACH Declaration</a>
EU RoHS Directive	Compliant with Exemptions
Mercury free	Yes
China RoHS Regulation	 <a href="#">China RoHS Declaration</a>
RoHS exemption information	 <a href="#">Yes</a>