

Product data sheet

Characteristics

56M42LE-GY

Clipsal - 56 Series, 40 Module Adaptor, 1 Aperture, Less Enclosure



Main

Range of product	Series 56
Range	Clipsal - 56 Series
Product brand	Clipsal
Product or component type	Enclosure
Plug, socket category	Low voltage
Outlet standard	Industrial
Colour	Grey (RAL 7035)

Complementary

Number of gangs	1 gang
Shape	Square
Device mounting	Surface
Cable entry number	0
Material	Polycarbonate: cover
Fixing mode	By screws
Tightening torque	0.8 N.m
Cable entry	3 entries of 25 mm diameter
Length	107 mm
Width	101 mm
Depth	39 mm
Height	107 mm
Net weight	0.22 kg
IP degree of protection	IP66
Targeted country	Australia

Environment

Ambient air temperature for operation	-25...75 °C
---------------------------------------	-------------

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	7.65 cm
Package 1 Width	9.95 cm
Package 1 Length	9.95 cm
Package 1 Weight	0.216 kg

Offer Sustainability

REACH Regulation	REACH Declaration
REACH free of SVHC	Yes
EU RoHS Directive	Compliant EU RoHS Declaration
Mercury free	Yes
China RoHS Regulation	China RoHS Declaration
RoHS exemption information	Yes