

Product data sheet

Characteristics

56P210-RO

56 Series Plug - 2 Pin - 10A - 250V



Main

Range	Clipsal - 56 Series
Range of product	Series 56
Product brand	Clipsal
Product or component type	Plug
Device application	Power supply

Complementary

[In] rated current	10 A
Poles description	1P + N
[Ue] rated operational voltage	250 V AC 50 Hz conforming to EN 60309-2
Colour	Orange (RAL 2004)
Material	Plastic
Plug, socket category	Low voltage
Material	PBT (polybutylene terephthalate): housing
Outlet standard	Industrial
Connections - terminals	Screw terminal 0.75...1 mm ²
Wire stripping length	10 Mm 35 mm
Contacts material	Pins: brass
Cable entry	Cable gland
Thread type	M20
Plug, socket, control station shape	Straight
Quality labels	RCM
Pin arrangement	D
Service life in hours	4 h
Net weight	0.14 kg
Height	67 mm
Width	67 mm
Depth	112.5 mm
Targeted country	Australia

Environment

Standards	AS/NZS 3112
IP degree of protection	IP66 conforming to AS 60529
Ambient air temperature for operation	-25...75 °C

Packing Units

Package 1 Weight	0.140 kg
------------------	----------

Offer Sustainability

Sustainable offer status	Green Premium product
EU RoHS Directive	Compliant EU RoHS Declaration
Mercury free	Yes
RoHS exemption information	Yes
China RoHS Regulation	China RoHS Declaration
Environmental Disclosure	Product Environmental Profile