

## Product data sheet

### Characteristics

# 56P310-EO

## 56 Series Plug - 3 Pin - 10A - 250V



### Main

Range	Clipsal - 56 Series
Range of product	Series 56
Product brand	Clipsal
Product or component type	Plug
Device application	Power supply
Number of poles	3

### Complementary

[In] rated current	10 A
Poles description	1P + N + E
[Ue] rated operational voltage	250 V AC 50 Hz conforming to EN 60309-2
Colour	Orange (RAL 2004)
Material	Plastic
Plug, socket category	Low voltage
Material	Polycarbonate: housing
Outlet standard	Industrial
Connections - terminals	Screw terminal 0.75...1 mm <sup>2</sup>
Wire stripping length	35 Mm 10 mm
Contacts material	Pins: brass
Cable entry	Cable gland
Thread type	M20
Plug, socket, control station shape	Straight
Quality labels	RCM
Pin arrangement	A
Duration	6 h
Net weight	0.12 kg
Height	67 mm
Width	67 mm
Depth	112.5 mm
Targeted country	Australia

### Environment

IP degree of protection	IP66
Standards	AS/NZS 3112
IP degree of protection	IP66 conforming to AS 60529
Ambient air temperature for operation	-25...75 °C

### Packing Units

Package 1 Weight	107.000 g
------------------	-----------

## Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	<a href="#">REACH Declaration</a>
EU RoHS Directive	Compliant <a href="#">EU RoHS Declaration</a>
Mercury free	Yes
RoHS exemption information	<a href="#">Yes</a>
China RoHS Regulation	<a href="#">China RoHS Declaration</a>
Environmental Disclosure	<a href="#">Product Environmental Profile</a>