

## Product data sheet

### Characteristics

# 56P510-EO

Clipsal - 56 Series, Plugs and Extension  
Sockets, Straight Plugs - IP66, 500V 10A - 5  
Round Pins



### Main

Range	Clipsal - 56 Series
Range of product	Series 56
Product brand	Clipsal
Product or component type	Plug
Device application	Power supply

### Complementary

[In] rated current	10 A
Poles description	3P + N + E
[Ue] rated operational voltage	500 V AC 50 Hz conforming to EN 60309-2
Colour	Orange (RAL 2004)
Material	Plastic
Plug, socket category	Low voltage
Material	Polycarbonate: housing
Outlet standard	Industrial
Connections - terminals	Screw terminal 1...6 mm <sup>2</sup>
Wire stripping length	45 Mm 12 mm
Contacts material	Pins: brass
Cable entry	Cable gland
Thread type	M25
Plug, socket, control station shape	Straight
Pin arrangement	Q
Duration	7 h
Net weight	0.32 kg
Height	78 mm
Width	78 mm
Depth	167 mm
Targeted country	Australia

### Environment

Standards	AS/NZS 3123
IP degree of protection	IP66 conforming to AS 60529
Ambient air temperature for operation	-25...75 °C

## Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	8.4 cm
Package 1 Width	9.8 cm
Package 1 Length	18.4 cm
Package 1 Weight	322.0 g

## Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	<a href="#"> REACH Declaration</a>
EU RoHS Directive	Compliant with Exemptions
China RoHS Regulation	<a href="#"> China RoHS Declaration</a>
RoHS exemption information	<a href="#"> Yes</a>
Environmental Disclosure	<a href="#"> Product Environmental Profile</a>
Circularity Profile	No need of specific recycling operations