

Product data sheet

Characteristics

56P532-EO

56 Series Plug - 5 Pin - 32A - 500V



Main

Range	Clipsal - 56 Series
Range of product	Series 56
Product brand	Clipsal
Product or component type	Plug
Device application	Power supply

Complementary

[In] rated current	32 A
Poles description	3P + N + E
[Ue] rated operational voltage	500 V AC 50 Hz conforming to EN 60309-2
Colour	Orange (RAL 2004)
Material	Plastic
Plug, socket category	Low voltage
Material	Polycarbonate: housing
Outlet standard	Industrial
Connections - terminals	Screw terminal 2.5...25 mm ²
Wire stripping length	20 Mm 50 mm
Contacts material	Pins: brass
Cable entry	Cable gland
Thread type	M40
Plug, socket, control station shape	Straight
Pin arrangement	S
Duration	7 h
Net weight	0.42 kg
Height	79 mm
Width	79 mm
Depth	168 mm
Targeted country	Australia

Environment

Standards	AS/NZS 3123
IP degree of protection	IP66 conforming to AS 60529
Ambient air temperature for operation	-25...75 °C

The information provided in this documentation contains general descriptions and/or technical characteristics of the performance of the products contained herein. This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications. It is the duty of any such user or integrator to perform the appropriate and complete risk analysis, evaluation and testing of the products with respect to the relevant specific application or use thereof. Neither Schneider Electric Industries SAS nor any of its affiliates or subsidiaries shall be responsible or liable for misuse of the information contained herein.

Packing Units

Package 1 Weight	419.000 g
Package 1 Height	91.000 mm
Package 1 width	90.000 mm
Package 1 Length	200.000 mm

Offer Sustainability

Sustainable offer status	Green Premium product
EU RoHS Directive	Compliant EU RoHS Declaration
Mercury free	Yes
RoHS exemption information	Yes
China RoHS Regulation	China RoHS Declaration
Environmental Disclosure	Product Environmental Profile