

Product data sheet

Characteristics

56PA440-EO

Clipsal - 56 Series, Plugs and Extension
Sockets, Angle Plugs - IP66, 500V 40A - 4
Round Pins



Main

Range	Clipsal - 56 Series
Range of product	Series 56
Product brand	Clipsal
Product or component type	Plug
Device application	Power supply

Complementary

[In] rated current	40 A
Poles description	3P + E
[Ue] rated operational voltage	500 V AC 50 Hz conforming to EN 60309-2
Colour	Body: orange (RAL 2004)
Material	Plastic
Plug, socket category	Low voltage
Material	Polycarbonate: housing
Outlet standard	Industrial
Connections - terminals	Screw terminal 2.5...25 mm ²
Wire stripping length	50 Mm 20 mm
Contacts material	Pins: brass
Cable entry	Cable gland
Thread type	M40
Plug, socket, control station shape	Angled
Pin arrangement	O
Duration	7 h
Net weight	0.5 kg
Height	78 mm
Width	130 mm
Depth	168 mm
Targeted country	Australia

Environment

Standards	AS/NZS 3123
IP degree of protection	IP66 conforming to AS 60529
Ambient air temperature for operation	-25...75 °C

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	9.2 cm
Package 1 Width	9.2 cm
Package 1 Length	19.9 cm
Package 1 Weight	427.0 g

Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	 REACH Declaration
EU RoHS Directive	Compliant with Exemptions
China RoHS Regulation	 China RoHS Declaration
RoHS exemption information	 Yes
Environmental Disclosure	 Product Environmental Profile
Circularity Profile	No need of specific recycling operations