

Product data sheet

Characteristics

56PB-GY

56 Series - Control Station - 1 Start - grey



Main

Range of product	Series 56
Range	Clipsal - 56 Series
Product brand	Clipsal
Product or component type	Switch
Device application	Control
Colour	Cover: grey

Complementary

[Us] rated supply voltage	Lamp: 500 V AC 50 Hz
[In] rated current	10 A
Colour	Grey
Poles description	1P
Control type	Push-button
Suitability for isolation	No
Connections - terminals	Screw terminal cable(s) 1...4 mm ² solid
Tightening torque	0.8 N.m
Cap/operator or lens colour	Green
Width	101 mm
Height	107 mm
Depth	76 mm
Net weight	0.34 kg
Marking	START
Targeted country	Australia

Environment

IP degree of protection	IP66
Ambient air temperature for operation	-25...75 °C
IP degree of protection	IP66 conforming to AS 60529
Standards	AS/NZS 3100 AS/NZS 3133

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Weight	0.36 kg
Package 1 Height	11 cm
Package 1 width	10.5 cm
Package 1 Length	10.5 cm

Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	REACH Declaration
EU RoHS Directive	Compliant EU RoHS Declaration
Mercury free	Yes
RoHS exemption information	Yes
China RoHS Regulation	China RoHS Declaration
Environmental Disclosure	Product Environmental Profile