

Product data sheet

Characteristics

56PB10T-GY

Push Button BLE Time Delay Switch, Clipsal - 56 Series, 10AX, 15A, 240V

Main

Range of product	Series 56
Range	Clipsal - 56 Series
Product brand	Clipsal
Product or component type	Time switch
Assembly Type	Complete switch
Device application	Control
Outlet standard deviation	Australian/New Zealand
Control button type	1 push-button
Colour	Grey (RAL 7035)
Plug, socket category	Low voltage

Complementary

Poles description	1P + N
Control type	Push-button
Number of poles	1
Installation Type	Surface
Material	Polycarbonate: cover
Tightening torque	0.8 N.m
Local signalling	without
[Ue] rated operational voltage	250 V AC 50 Hz
Rated current	15 A 10 AX
Protection type	Without protection
Marking	Without marking
Connections - terminals	Screw terminals 4 x 1.5 mm ² rigid or stranded Screw terminals 3 x 2.5 mm ² rigid or stranded
Targeted country	Australia
Height	101 mm
Width	101 mm
Depth	112 mm
Net weight	0.46 kg
Cable entry	3 entries of 25 mm diameter
Switch function	1-pole

Environment

Ambient air temperature for operation	0...25 °C
Outlet standard	Industrial
IP degree of protection	IP66 conforming to AS 60529
Standards	AS/NZS 3133 AS/NZS 3123

The information provided in this documentation contains general descriptions and/or technical characteristics of the performance of the products contained herein. This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications. It is the duty of any such user or integrator to perform the appropriate and complete risk analysis, evaluation and testing of the products with respect to the relevant specific application or use thereof. Neither Schneider Electric Industries SAS nor any of its affiliates or subsidiaries shall be responsible or liable for misuse of the information contained herein.

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	11.25 cm
Package 1 Width	10.35 cm
Package 1 Length	10.65 cm
Package 1 Weight	0.464 kg

Offer Sustainability

Packaging without single use plastic	No
Packaging made with recycled cardboard	Yes
REACH Regulation	REACH Declaration
EU RoHS Directive	Compliant with Exemptions
Mercury free	Yes
RoHS exemption information	Yes
China RoHS Regulation	China RoHS Declaration
Environmental Disclosure	Product Environmental Profile
Circularity Profile	End Of Life Information
Take-back	No