

Product data sheet

Characteristics

56PB10T-GY

56 Series - push button BLE time delay switch -
10AX - 15A - 240V - grey



Main

Range of product	Series 56
Range	Clipsal - 56 Series
Product brand	Clipsal
Product or component type	Time switch
Device presentation	Complete switch
Device application	Control
Colour	Grey (RAL 7035)
Plug, socket category	Low voltage
Outlet standard	Australian/New Zealand
Control button type	1 push-button

Complementary

Switch function	1-pole
Poles description	1P + N
Control type	Push-button
Number of poles	1
Device mounting	Surface
Connections - terminals	Screw terminals 4 x 1.5 mm ² rigid or stranded Screw terminals 3 x 2.5 mm ² rigid or stranded
Cable entry	3 entries of 25 mm diameter
Material	Polycarbonate: cover
Tightening torque	0.8 N.m
Local signalling	without
[Ue] rated operational voltage	250 V AC 50 Hz
Rated current	15 A 10 AX
Protection type	Without protection
Marking	Without marking
Height	101 mm
Width	101 mm
Depth	112 mm
Net weight	0.46 kg
Targeted country	Australia

Environment

Ambient air temperature for operation	0...25 °C
Outlet standard	Industrial
IP degree of protection	IP66 conforming to AS 60529
Standards	AS/NZS 3133 AS/NZS 3123

Packing Units

Package 1 Weight	0.464 kg
------------------	----------