

Product data sheet

Characteristics

56PBLE-GY

Clipsal - 56 Series, Control Station IP66 1Xstart Less Enclosure



Main

Range of product	Series 56
Range	Clipsal - 56 Series
Product brand	Clipsal
Product or component type	Switch
Device application	Control
Colour	Cover: grey

Complementary

[Us] rated supply voltage	Lamp: 500 V AC 50 Hz
[In] rated current	10 A
Colour	Grey
Poles description	1P
Control type	Push-button
Suitability for isolation	No
Connections - terminals	Screw terminal cable(s) 1...4 mm ² solid
Tightening torque	0.8 N.m
Cap/operator or lens colour	Green
Width	101 mm
Height	107 mm
Depth	59 mm
Net weight	0.179 kg
Marking	START
Targeted country	Australia

Environment

IP degree of protection	IP66
Ambient air temperature for operation	-25...75 °C
IP degree of protection	IP66 conforming to AS 60529
Standards	AS/NZS 3100 AS/NZS 3133

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	10.5 cm
Package 1 Width	10.0 cm
Package 1 Length	10.5 cm
Package 1 Weight	167.0 g

Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	 REACH Declaration
EU RoHS Directive	Compliant with Exemptions
China RoHS Regulation	 China RoHS Declaration
RoHS exemption information	 Yes
Environmental Disclosure	 Product Environmental Profile
Circularity Profile	No need of specific recycling operations