

Product data sheet

Characteristics

56PBLE-GY

56 Series - Control Station - 1 Start - Less Enclosure - grey



Main

| | |
|---------------------------|---------------------|
| Range of product | Series 56 |
| Range | Clipsal - 56 Series |
| Product brand | Clipsal |
| Product or component type | Switch |
| Device application | Control |
| Colour | Cover: grey |

Complementary

| | |
|-----------------------------|---|
| [Us] rated supply voltage | Lamp: 500 V AC 50 Hz |
| [In] rated current | 10 A |
| Colour | Grey |
| Poles description | 1P |
| Control type | Push-button |
| Suitability for isolation | No |
| Connections - terminals | Screw terminal cable(s) 1...4 mm ² solid |
| Tightening torque | 0.8 N.m |
| Cap/operator or lens colour | Green |
| Width | 101 mm |
| Height | 107 mm |
| Depth | 59 mm |
| Net weight | 0.179 kg |
| Marking | START |
| Targeted country | Australia |

Environment

| | |
|---------------------------------------|-----------------------------|
| IP degree of protection | IP66 |
| Ambient air temperature for operation | -25...75 °C |
| IP degree of protection | IP66 conforming to AS 60529 |
| Standards | AS/NZS 3100 AS/NZS 3133 |

Packing Units

| | |
|------------------------------|---------|
| Unit Type of Package 1 | PCE |
| Number of Units in Package 1 | 1 |
| Package 1 Height | 10.5 cm |
| Package 1 Width | 10.0 cm |
| Package 1 Length | 10.5 cm |
| Package 1 Weight | 167.0 g |

Offer Sustainability

| | |
|----------------------------|---|
| Sustainable offer status | Green Premium product |
| REACH Regulation | REACH Declaration |
| EU RoHS Directive | Compliant EU RoHS Declaration |
| Mercury free | Yes |
| RoHS exemption information | Yes |
| China RoHS Regulation | China RoHS Declaration |
| Environmental Disclosure | Product Environmental Profile |