

Product data sheet

Characteristics

56PBS1-RW

Clipsal - 56 Series, Push Button Control Station, 3A, Emergency Stop



Main

Range of product	Series 56
Range	Clipsal - 56 Series
Product brand	Clipsal
Product or component type	Switch
Device application	Control
Colour	Cover: white

Complementary

[Us] rated supply voltage	Lamp: 500 V AC 50 Hz
[In] rated current	10 A
Colour	Resistant white electric
Poles description	1P
Control type	Push-button
Suitability for isolation	No
Connections - terminals	Screw terminal cable(s) 1...4 mm ² solid
Tightening torque	0.8 N.m
Cap/operator or lens colour	Red
Width	101 mm
Height	107 mm
Depth	102 mm
Net weight	0.4 kg
Marking	EMERGENCY STOP
Targeted country	Australia

Environment

IP degree of protection	IP66
Ambient air temperature for operation	-25...75 °C
IP degree of protection	IP66 conforming to AS 60529
Standards	AS/NZS 3100 AS/NZS 3133

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Weight	0.4 kg

Offer Sustainability

REACH Regulation	 REACH Declaration
EU RoHS Directive	Compliant with Exemptions
China RoHS Regulation	 China RoHS Declaration
RoHS exemption information	 Yes