

## Product data sheet

### Characteristics

# 56PBS2-GY

## Clipsal - 56 Series, Push Button Control Station, 3A, Latching



### Main

Range of product	Series 56
Range	Clipsal - 56 Series
Product brand	Clipsal
Product or component type	Switch
Device application	Control
Colour	Cover: grey

### Complementary

[Us] rated supply voltage	Lamp: 500 V AC 50 Hz
[In] rated current	10 A
Colour	Grey
Poles description	1P
Control type	Push-button
Suitability for isolation	No
Connections - terminals	Screw terminal cable(s) 1...4 mm <sup>2</sup> solid
Tightening torque	0.8 N.m
Cap/operator or lens colour	Red
Width	101 mm
Height	107 mm
Depth	102 mm
Net weight	0.36 kg
Marking	STOP
Targeted country	Australia

### Environment

IP degree of protection	IP66
Ambient air temperature for operation	-25...75 °C
IP degree of protection	IP66 conforming to AS 60529
Standards	AS/NZS 3100 AS/NZS 3133

### Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	10.4 cm
Package 1 Width	10.4 cm
Package 1 Length	10.6 cm
Package 1 Weight	358.0 g

## Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	<a href="#">REACH Declaration</a>
EU RoHS Directive	Compliant <a href="#">EU RoHS Declaration</a>
Mercury free	Yes
China RoHS Regulation	<a href="#">China RoHS Declaration</a>
RoHS exemption information	<a href="#">Yes</a>
Environmental Disclosure	<a href="#">Product Environmental Profile</a>