

## Product data sheet

### Characteristics

# 56PO520-EO

## Pendant Outlets, IP66, 500V 20A, 5 Round Pins



### Main

Range of product	Series 56
Range	Clipsal - 56 Series
Product brand	Clipsal
Product or component type	Pendant outlet
Device application	Power supply
Colour	Orange (RAL 2004)

### Complementary

Plug, socket category	Low voltage
Plug, socket, control station shape	Straight
Mounting mode	External mounting
Mounting support	Pendant
[In] rated current	20 A
[Ue] rated operational voltage	500 V AC 50 Hz conforming to EN 60309-2
Poles description	3P + N + E
Voltage colour	Black
Duration	7 h
Material	Polycarbonate: housing
Contacts material	Sleeves: brass
Connections - terminals	Screw terminals 1...6 mm <sup>2</sup>
Socket number	1
Socket-outlet type	R
Outlet standard	Industrial
Cable outer diameter	7...16 mm
Cable entry	Cable gland
Thread type	M25
Net weight	0.36 kg
Depth	209 mm
Width	90 mm
Height	90 mm
Targeted country	Australia

### Environment

IP degree of protection	IP66 conforming to AS 60529
Ambient air temperature for operation	-25...75 °C
Standards	AS/NZS 3120

The information provided in this documentation contains general descriptions and/or technical characteristics of the performance of the products contained herein. This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications. It is the duty of any such user or integrator to perform the appropriate and complete risk analysis, evaluation and testing of the products with respect to the relevant specific application or use thereof. Neither Schneider Electric Industries SAS nor any of its affiliates or subsidiaries shall be responsible or liable for misuse of the information contained herein.

## Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	8.2 cm
Package 1 Width	9.5 cm
Package 1 Length	17.5 cm
Package 1 Weight	347.0 g

## Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	<a href="#">REACH Declaration</a>
EU RoHS Directive	Compliant <a href="#">EU RoHS Declaration</a>
Mercury free	Yes
China RoHS Regulation	<a href="#">China RoHS Declaration</a>
RoHS exemption information	<a href="#">Yes</a>
Environmental Disclosure	<a href="#">Product Environmental Profile</a>