

Product data sheet

Characteristics

56SC432RC-GY

56 Series Switched Socket Outlet with RCD -
32A - 4 Pin - 500V - 30mA- Grey



Main

Range of product	Series 56
Range	Clipsal - 56 Series
Product brand	Clipsal
Product or component type	Socket-outlet with residual current device
Device application	Power supply
Colour	Grey (RAL 7035)

Complementary

Number of poles	4
Control type	Push-button
Number of modules	3
Number of power socket outlets	1 protective cover
[In] rated current	32 A
[Ue] rated operational voltage	500 V AC 50 Hz
Network number of phases	3 phases
Number of gangs	4 gangs
Installation direction	Vertical
Device mounting	Surface
Material	Polycarbonate
Connections - terminals	Screw terminals cable(s) 4...16 mm ²
Depth	135 mm
Width	204 mm
Height	204 mm
Net weight	2.212 kg
Targeted country	Australia

Environment

Ambient air temperature for operation	-25...75 °C
IP degree of protection	IP66

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Weight	2116 g
Package 1 Height	119 mm
Package 1 width	205 mm
Package 1 Length	210 mm

Offer Sustainability

Sustainable offer status	Green Premium product
EU RoHS Directive	Compliant EU RoHS Declaration
Mercury free	Yes
RoHS exemption information	Yes
China RoHS Regulation	China RoHS Declaration
Environmental Disclosure	Product Environmental Profile