

Product data sheet

Characteristics

56SC520RC-GY

RCD Protected Switched Socket Outlet, Clipsal
 - 56 Series, 500V 20A 5 Round PIN, IP66 3
 Pole, 30mA RCD



Main

Range of product	Series 56
Range	Clipsal - 56 Series
Product brand	Clipsal
Product or component type	Socket-outlet with residual current device
Device application	Power supply
Colour	Grey (RAL 7035)

Complementary

Number of poles	5
Control type	Push-button
Number of modules	3
Number of power socket outlets	1 protective cover
[In] rated current	20 A
[Ue] rated operational voltage	500 V AC 50 Hz
Network number of phases	3 phases
Number of gangs	4 gangs
Installation direction	Vertical
Device mounting	Surface
Material	Polycarbonate
Connections - terminals	Screw terminals cable(s) 1.5...16 mm ²
Depth	135 mm
Width	204 mm
Height	204 mm
Net weight	2.04 kg
Targeted country	Australia

Environment

Ambient air temperature for operation	-25...75 °C
IP degree of protection	IP66
Earth-leakage protection class	Class A

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	12.0 cm
Package 1 Width	20.8 cm
Package 1 Length	20.8 cm
Package 1 Weight	1.944 kg

Offer Sustainability

REACH Regulation	REACH Declaration
EU RoHS Directive	Compliant with Exemptions
China RoHS Regulation	China RoHS Declaration
RoHS exemption information	Yes