

## Product data sheet

### Characteristics

# 56SC540RC-GY

## Clipsal - 56 Series, Socket Outlet RCD



### Main

|                           |  |
|---------------------------|--|
| Range                     | Clipsal - 56 Series                        |
| Product or component type | Socket-outlet with residual current device |
| Device application        | Power supply                               |
| Colour                    | Grey (RAL 7035)                            |

### Complementary

|                                |   |
|--------------------------------|---|
| Control type                   | Push-button                                     |
| [In] rated current             | 40 A  |
| [Ue] rated operational voltage | 500 V AC 50 Hz                                  |
| Network number of phases       | 3 phases  |
| Number of gangs                | 4 gangs   |
| Installation direction         | Vertical  |
| Material                       | Polycarbonate                                   |
| Connections - terminals        | Screw terminal cable(s) 10...16 mm <sup>2</sup> |
| Mounting mode                  | Surface mounted                                 |
| Depth                          | 135 mm  |
| Width                          | 204 mm  |
| Height                         | 204 mm  |
| Net weight                     | 2.34 kg   |
| Targeted country               | Australia                                       |

### Environment

|                                       |             |
|---------------------------------------|-------------|
| Ambient air temperature for operation | -25...75 °C |
| IP degree of protection               | IP66        |

### Packing Units

|                              |          |
|------------------------------|----------|
| Unit Type of Package 1       | PCE      |
| Number of Units in Package 1 | 1        |
| Package 1 Height             | 11.35 cm |
| Package 1 Width              | 20.05 cm |
| Package 1 Length             | 20.65 cm |
| Package 1 Weight             | 2401.0 g |
| Unit Type of Package 2       | CAR      |
| Number of Units in Package 2 | 5        |
| Package 2 Height             | 21.0 cm  |
| Package 2 Width              | 34.8 cm  |
| Package 2 Length             | 44.5 cm  |
| Package 2 Weight             | 12.39 kg |

## Offer Sustainability

|                            |   |
|----------------------------|---|
| Sustainable offer status   | Green Premium product                         |
| REACH Regulation           | <a href="#">REACH Declaration</a>             |
| EU RoHS Directive          | Compliant <a href="#">EU RoHS Declaration</a> |
| Mercury free               | Yes   |
| China RoHS Regulation      | <a href="#">China RoHS Declaration</a>        |
| RoHS exemption information | <a href="#">Yes</a>                           |
| Environmental Disclosure   | <a href="#">Product Environmental Profile</a> |