

Product data sheet

Characteristics

56SO310L-CG

Clipsal - 56 Series, Socket Outlets, Surface
Sockets - IP66, 250V 10A - 2 Flat Pins and
Round Earth



Main

| | |
|---------------------------|------------------------|
| Range of product | Series 56 |
| Range | Clipsal - 56 Series |
| Product brand | Clipsal |
| Product or component type | Socket-outlet |
| Device application | Power supply |
| Colour | Chemical grey |
| Outlet standard deviation | Australian/New Zealand |

Complementary

| | |
|-------------------------------------|---|
| Plug, socket category | Low voltage |
| Plug, socket, control station shape | Straight |
| Device mounting | Surface |
| Mounting mode | External mounting |
| [In] rated current | 10 A |
| [Ue] rated operational voltage | 250 V AC 50 Hz conforming to EN 60309-2 |
| Poles description | 1P + N + E |
| Voltage colour | Blue |
| Duration | 6 h |
| Material | ABS (acrylonitrile butadiene-styrene); cover |
| Contacts material | Screws: brass |
| Connections - terminals | Screw terminals 1.5...6 mm ² rigid or stranded cable |
| Connections - terminals | Screw terminal |
| Tightening torque | 0.8 N.m |
| Socket number | 1 |
| Socket-outlet type | C |
| Outlet standard | Industrial |
| Cable outer diameter | 9...29 mm |
| Net weight | 0.3 kg |
| Depth | 77 mm |
| Width | 101 mm |
| Height | 107 mm |
| Targeted country | Australia |

Environment

| | |
|---------------------------------------|------------------------------|
| IP degree of protection | IP66 conforming to AS 60529 |
| Ambient air temperature for operation | -25...75 °C |
| Standards | AS/NZS 4417.1 AS/NZS 3112 |

Packing Units

| | |
|------------------------------|---------|
| Unit Type of Package 1 | PCE |
| Number of Units in Package 1 | 1 |
| Package 1 Height | 8.7 cm |
| Package 1 Width | 10.5 cm |
| Package 1 Length | 10.5 cm |
| Package 1 Weight | 398.0 g |

Offer Sustainability

| | |
|----------------------------|--|
| REACH Regulation | REACH Declaration |
| EU RoHS Directive | Compliant with Exemptions |
| China RoHS Regulation | China RoHS Declaration |
| RoHS exemption information | Yes |