

Product data sheet

Characteristics

56SO310LE-RW

56 Series Socket - 3 Pin - 10A - 250V - Less Enclosure - White



Main

Range of product	Series 56
Range	Clipsal - 56 Series
Product brand	Clipsal
Product or component type	Socket-outlet
Device application	Power supply
Colour	White (RAL 9003)
Outlet standard	Australian/New Zealand

Complementary

Plug, socket category	Low voltage
Device mounting	Surface
Mounting mode	External mounting
[In] rated current	10 A
[Ue] rated operational voltage	250 V AC 50 Hz conforming to EN 60309-2
Poles description	1P + N + E
Voltage colour	Blue
Duration	6 h
Material	PC + PET: cover
Contacts material	Screws: brass
Connections - terminals	Screw terminals 1.5...6 mm ² rigid or stranded cable
Connections - terminals	Screw terminal
Tightening torque	0.8 N.m
Socket number	1
Socket-outlet type	C
Outlet standard	Industrial
Net weight	0.222 kg
Depth	64 mm
Width	101 mm
Height	107 mm
Targeted country	Australia

Environment

IP degree of protection	IP66 conforming to AS 60529
Ambient air temperature for operation	-25...75 °C
Standards	AS/NZS 4417.1 AS/NZS 3112

Packing Units

Package 1 Weight	219 g
------------------	-------

Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	REACH Declaration
EU RoHS Directive	Compliant EU RoHS Declaration
Mercury free	Yes
RoHS exemption information	Yes
China RoHS Regulation	China RoHS Declaration
Environmental Disclosure	Product Environmental Profile