

Product data sheet

Characteristics

56SO320-GY

56 Series Socket - 3 Pin - 20A - 250V - Grey



Main

Range of product	Series 56
Range	Clipsal - 56 Series
Product brand	Clipsal
Product or component type	Socket-outlet
Device application	Power supply
Colour	Grey (RAL 7035)
Outlet standard	Australian/New Zealand

Complementary

Plug, socket category	Low voltage
Device mounting	Surface
Mounting mode	External mounting
[In] rated current	20 A
[Ue] rated operational voltage	250 V AC 50 Hz conforming to EN 60309-2
Poles description	1P + N + E
Voltage colour	Blue
Duration	6 h
Material	Polycarbonate: cover
Contacts material	Screws: brass
Connections - terminals	Screw terminals 2.5...6 mm ² rigid or stranded cable
Tightening torque	0.8 N.m
Socket number	1
Socket-outlet type	H
Outlet standard	Industrial
Product weight	0.58 kg
Depth	102 mm
Width	101 mm
Height	107 mm
Targeted country	Australia

Environment

Ambient air temperature for operation	-25...75 °C
Standards	AS/NZS 3112

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Weight	576 g
Package 1 Height	110 mm
Package 1 width	100 mm
Package 1 Length	105 mm

Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	REACH Declaration
EU RoHS Directive	Compliant EU RoHS Declaration
Mercury free	Yes
RoHS exemption information	Yes
China RoHS Regulation	China RoHS Declaration
Environmental Disclosure	Product Environmental Profile