

## Product data sheet

### Characteristics

# 56SO332/6-GY

56 Series Socket - 3 Pin - 32A - 250V - Grey



#### Main

Range of product	Series 56
Range	Clipsal - 56 Series
Product brand	Clipsal
Product or component type	Socket-outlet
Device application	Power supply
Colour	Grey (RAL 7035)
Outlet standard	Australian/New Zealand

#### Complementary

Plug, socket category	Low voltage
Device mounting	Surface
Mounting mode	External mounting
[In] rated current	32 A
[Ue] rated operational voltage	250 V AC 50 Hz conforming to EN 60309-2
Poles description	1P + N + E
Voltage colour	Blue
Material	Polycarbonate: cover
Contacts material	Screws: brass
Connections - terminals	Screw terminals rigid or stranded cable
Tightening torque	0.8 N.m
Socket number	1
Socket-outlet type	M
Outlet standard	Industrial
Net weight	0.58 kg
Width	101 mm
Height	107 mm
Targeted country	Australia

#### Environment

Ambient air temperature for operation	-25...75 °C
Standards	IEC 309

#### Packing Units

Package 1 Weight	561.000 g
Package 1 Height	104.000 mm
Package 1 width	111.000 mm
Package 1 Length	138.000 mm

## Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	<a href="#">REACH Declaration</a>
EU RoHS Directive	Compliant <a href="#">EU RoHS Declaration</a>
Mercury free	Yes
RoHS exemption information	<a href="#">Yes</a>
China RoHS Regulation	<a href="#">China RoHS Declaration</a>
Environmental Disclosure	<a href="#">Product Environmental Profile</a>