

Product data sheet

Characteristics

56SO332/6LE-GY

56 Series Socket - 3 Pin - 32A - 250V - Less Enclosure - Grey



Main

Range of product	Series 56
Range	Clipsal - 56 Series
Product brand	Clipsal
Product or component type	Socket-outlet
Device application	Power supply
Colour	Grey (RAL 7035)
Outlet standard	Australian/New Zealand

Complementary

Plug, socket category	Low voltage
Device mounting	Surface
Mounting mode	External mounting
[In] rated current	32 A
[Ue] rated operational voltage	250 V AC 50 Hz conforming to EN 60309-2
Poles description	1P + N + E
Voltage colour	Blue
Duration	6 h
Material	Polycarbonate: cover
Contacts material	Screws: brass
Connections - terminals	Screw terminals rigid or stranded cable
Tightening torque	0.8 N.m
Socket number	1
Socket-outlet type	M
Outlet standard	Industrial
Cable entry	Tapped entry
Net weight	0.3 kg
Depth	39 mm
Width	101 mm
Height	107 mm
Targeted country	Australia

Environment

Ambient air temperature for operation	-25...75 °C
Standards	IEC 309

Packing Units

Package 1 Weight	296.000 g
Package 1 Height	100.000 mm
Package 1 width	106.000 mm
Package 1 Length	106.000 mm

Offer Sustainability

Sustainable offer status	Green Premium product
EU RoHS Directive	Compliant EU RoHS Declaration
Mercury free	Yes
RoHS exemption information	Yes
China RoHS Regulation	China RoHS Declaration
Environmental Disclosure	Product Environmental Profile