

## Product data sheet

### Characteristics

# 56SO332G

Clipsal - 56 Series, Internal Socket Housings,  
250V, 32A, 3 Round Pin



#### Main

Range of product	Series 56
Range	Clipsal - 56 Series
Product brand	Clipsal
Product or component type	Socket-outlet
Device application	Power supply
Colour	Grey (RAL 7035)
Outlet standard	Australian/New Zealand

#### Complementary

Plug, socket category	Low voltage
Device mounting	Surface
[In] rated current	32 A
[Ue] rated operational voltage	250 V AC 50 Hz conforming to EN 60309-2
Poles description	1P + N + E
Voltage colour	Blue
Material	Polycarbonate: cover
Contacts material	Screws: brass
Connections - terminals	Screw terminals 6...16 mm <sup>2</sup> rigid or stranded cable
Tightening torque	0.8 N.m
Socket number	1
Socket-outlet type	I
Outlet standard	Industrial
Net weight	0.3 kg
Service life in hours	9 h
Targeted country	Australia

#### Environment

Ambient air temperature for operation	-25...75 °C
Standards	AS/NZS 3112

#### Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	60 cm
Package 1 Width	85 cm
Package 1 Length	80 cm
Package 1 Weight	0.3 kg
Unit Type of Package 2	CAR
Number of Units in Package 2	30
Package 2 Height	225 cm

Package 2 Width	305 cm
Package 2 Length	430 cm
Package 2 Weight	9 kg

### Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	<a href="#">REACH Declaration</a>
EU RoHS Directive	Compliant <a href="#">EU RoHS Declaration</a>
Mercury free	Yes
China RoHS Regulation	<a href="#">China RoHS Declaration</a>
RoHS exemption information	<a href="#">Yes</a>
Environmental Disclosure	<a href="#">Product Environmental Profile</a>