

Product data sheet

Characteristics

56SO432/3LE-GY

Socket Outlet, 4 PIN Round, Less Enclosure, 32A



Main

Range of product	Series 56
Range	Clipsal - 56 Series
Product brand	Clipsal
Product or component type	Socket-outlet
Device application	Power supply
Colour	Grey (RAL 7035)
Outlet standard deviation	Australian/New Zealand

Complementary

Plug, socket category	Low voltage
Device mounting	Surface
Mounting mode	External mounting
[In] rated current	32 A
[Ue] rated operational voltage	500 V AC 50 Hz conforming to EN 60309-2
Poles description	3P + E
Voltage colour	Red
Duration	6 h
Material	Polycarbonate: cover
Contacts material	Screws: brass
Connections - terminals	Screw terminals rigid or stranded cable
Tightening torque	0.8 N.m
Socket number	1
Outlet standard	Industrial
Net weight	0.32 kg
Depth	39 mm
Width	101 mm
Height	107 mm
Targeted country	Australia

Environment

Ambient air temperature for operation	-25...75 °C
Standards	IEC 309

Packing Units

Unit Type of Package 1	Db
Number of Units in Package 1	1
Package 1 Height	10.6 cm
Package 1 Width	10.0 cm
Package 1 Length	10.6 cm
Package 1 Weight	310.0 g

Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	REACH Declaration
EU RoHS Directive	Compliant EU RoHS Declaration
Mercury free	Yes
China RoHS Regulation	China RoHS Declaration
RoHS exemption information	Yes
Environmental Disclosure	Product Environmental Profile