

## Product data sheet

### Characteristics

# 56SO432G

Internal Socket Housings, Clipsal - 56 Series,  
500V, 32A, 4 Round Pin

### Main

Range of product	Series 56
Range	Clipsal - 56 Series
Product brand	Clipsal
Product or component type	Socket-outlet
Device application	Power supply
Colour	Grey (RAL 7035)
Outlet standard deviation	Australian/New Zealand

### Complementary

Plug, socket category	Low voltage
Device mounting	Surface
Mounting mode	External mounting
[In] rated current	32 A
[Ue] rated operational voltage	500 V AC 50 Hz conforming to EN 60309-2
Poles description	3P + E
Voltage colour	Black
Duration	7 h
Material	Polycarbonate: cover
Contacts material	Screws: brass
Connections - terminals	Screw terminals 4...16 mm <sup>2</sup> rigid or stranded cable
Tightening torque	0.8 N.m
Socket number	1
Socket-outlet type	N
Outlet standard	Industrial
Net weight	0.25 kg
Targeted country	Australia


### Environment

Ambient air temperature for operation	-25...75 °C
Standards	AS/NZS 3112

### Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	8.4 cm
Package 1 Width	10 cm
Package 1 Length	10 cm
Package 1 Weight	0.188 kg

## Offer Sustainability

EU RoHS Directive	Compliant with Exemptions
China RoHS Regulation	 <a href="#">China RoHS Declaration</a>
RoHS exemption information	 <a href="#">Yes</a>