

## Product data sheet

### Characteristics

# 56SO450G

Clipsal, Internal Socket Housings, 500V, 50A, 4 Round Pin



#### Main

Range of product	Series 56
Product brand	Clipsal

#### Complementary

Device mounting	Surface
Mounting mode	External mounting
[In] rated current	50 A
[Ue] rated operational voltage	500 V 50/60 Hz conforming to EN 60309-2
Voltage colour	Black
Duration	7 h
Material	PVC (polyvinyl chloride)
Socket number	1
Socket-outlet type	P

#### Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Weight	0.001 kg

#### Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	<a href="#">REACH Declaration</a>
EU RoHS Directive	Compliant <a href="#">EU RoHS Declaration</a>
Mercury free	Yes
China RoHS Regulation	<a href="#">China RoHS Declaration</a>
RoHS exemption information	<a href="#">Yes</a>
Environmental Disclosure	<a href="#">Product Environmental Profile</a>
WEEE	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins

The information provided in this documentation contains general descriptions and/or technical characteristics of the performance of the products contained herein. This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications. It is the duty of any such user or integrator to perform the appropriate and complete risk analysis, evaluation and testing of the products with respect to the relevant specific application or use thereof. Neither Schneider Electric Industries SAS nor any of its affiliates or subsidiaries shall be responsible or liable for misuse of the information contained herein.