

Product data sheet

Characteristics

56SO450G

Internal Socket Housings, Clipsal - 56 Series,
500V, 50A, 4 Round Pin

Main

Range of product	Series 56
Product brand	Clipsal



Complementary

Device mounting	Surface
Mounting mode	External mounting
[In] rated current	50 A
[Ue] rated operational voltage	500 V 50/60 Hz conforming to EN 60309-2
Voltage colour	Black
Duration	7 h
Material	PVC (polyvinyl chloride)
Socket number	1
Socket-outlet type	P

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Weight	0.001 kg

Offer Sustainability

EU RoHS Directive	Compliant with Exemptions
China RoHS Regulation	 China RoHS Declaration
RoHS exemption information	 Yes
WEEE	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins

The information provided in this documentation contains general descriptions and/or technical characteristics of the performance of the products contained herein. This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications. It is the duty of any such user or integrator to perform the appropriate and complete risk analysis, evaluation and testing of the products with respect to the relevant specific application or use thereof. Neither Schneider Electric Industries SAS nor any of its affiliates or subsidiaries shall be responsible or liable for misuse of the information contained herein.