

Product data sheet

Characteristics

56SO4ELP10-RO

Clipsal - 56 Series, Socket Outlet RCD
Portable 10A

Main

Range of product	Series 56
Range	Clipsal - 56 Series
Product brand	Clipsal
Product or component type	Socket-outlet with residual current device
Device application	Power supply
Colour	Orange (RAL 2004)

Complementary

Control type	Push-button
[In] rated current	10 A
[Ue] rated operational voltage	250 V AC 50 Hz
Network number of phases	1 phase
Number of gangs	6 gangs
Material	PC + PET
Net weight	3.2 kg
Depth	105 mm
Width	294 mm
Height	243 mm
Targeted country	Australia

Environment

IP degree of protection	IP56
Ambient air temperature for operation	-25...75 °C
Earth-leakage protection class	Class A

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	13.8 cm
Package 1 Width	25.8 cm
Package 1 Length	40.6 cm
Package 1 Weight	3.18 kg

Offer Sustainability

REACH Regulation	 REACH Declaration
EU RoHS Directive	Compliant with Exemptions
China RoHS Regulation	 China RoHS Declaration
RoHS exemption information	 Yes