

Product data sheet

Characteristics

56SO516/6LE-GY

56 Series Socket - 5 Pin - 16A - 500V - Less Enclosure - Grey



Main

Range	Clipsal - 56 Series
Product or component type	Socket-outlet
Device application	Power supply
Colour	Grey (RAL 7035)

Complementary

Plug, socket category	Low voltage
Mounting mode	Surface mounted
[In] rated current	16 A
[Ue] rated operational voltage	500 V AC 50 Hz
Poles description	3P + N + E
Secondary keyway clockwise position	6 h
Material	Polycarbonate: cover
Contacts material	Screws: brass
Connections - terminals	Screw terminals rigid or stranded cable
Tightening torque	0.8 N.m
Outlet standard	Industrial
Net weight	0.292 kg
Length	107 mm
Width	101 mm
Targeted country	Australia

Environment

IP degree of protection	IP66 conforming to IEC 60529
Ambient air temperature for operation	-25...75 °C
Standards	IEC 309-1

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Weight	0.292 kg
Package 1 Height	10.5 cm
Package 1 width	10.5 cm
Package 1 Length	10 cm

Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	REACH Declaration
EU RoHS Directive	Compliant EU RoHS Declaration
Mercury free	Yes
RoHS exemption information	Yes
China RoHS Regulation	China RoHS Declaration
Environmental Disclosure	Product Environmental Profile