

Product data sheet

Characteristics

56SO520LE-GY

56 Series Socket - 5 Pin - 20A - 500V - Less Enclosure - Grey



Main

| | |
|---------------------------|------------------------|
| Range of product | Series 56 |
| Range | Clipsal - 56 Series |
| Product brand | Clipsal |
| Product or component type | Socket-outlet |
| Device application | Power supply |
| Colour | Grey (RAL 7035) |
| Outlet standard | Australian/New Zealand |

Complementary

| | |
|--------------------------------|---|
| Plug, socket category | Low voltage |
| Device mounting | Surface |
| Mounting mode | External mounting |
| [In] rated current | 20 A |
| [Ue] rated operational voltage | 500 V AC 50 Hz conforming to EN 60309-2 |
| Poles description | 3P + N + E |
| Voltage colour | Black |
| Duration | 7 h |
| Material | Polycarbonate: cover |
| Contacts material | Screws: brass |
| Connections - terminals | Screw terminals 2.5...6 mm ² rigid or stranded cable |
| Tightening torque | 0.8 N.m |
| Socket number | 1 |
| Socket-outlet type | R |
| Outlet standard | Industrial |
| Net weight | 0.3 kg |
| Depth | 71 mm |
| Width | 101 mm |
| Height | 107 mm |
| Targeted country | Australia |

Environment

| | |
|---------------------------------------|-------------|
| Ambient air temperature for operation | -25...75 °C |
| Standards | AS/NZS 3112 |

Packing Units

| | |
|------------------|------------|
| Package 1 Weight | 296.000 g |
| Package 1 Height | 80.000 mm |
| Package 1 width | 100.000 mm |
| Package 1 Length | 100.000 mm |

Offer Sustainability

| | |
|----------------------------|---|
| EU RoHS Directive | Under investigation |
| Toxic heavy metal free | Yes |
| Mercury free | Yes |
| RoHS exemption information | Yes |
| China RoHS Regulation | China RoHS Declaration |
| Environmental Disclosure | Product Environmental Profile |