

## Product data sheet

### Characteristics

# 56SO532G

## 56 Series Socket - 5 Pin - 32A - 500V



### Main

|                           |                        |
|---------------------------|------------------------|
| Range of product          | Series 56              |
| Range                     | Clipsal - 56 Series    |
| Product brand             | Clipsal                |
| Product or component type | Socket-outlet          |
| Device application        | Power supply           |
| Colour                    | Grey (RAL 7035)        |
| Outlet standard           | Australian/New Zealand |

### Complementary

|                                |  |
|--------------------------------|--|
| Plug, socket category          | Low voltage  |
| Device mounting                | Surface  |
| [In] rated current             | 32 A   |
| [Ue] rated operational voltage | 500 V AC 50 Hz conforming to EN 60309-2                        |
| Poles description              | 3P + N + E   |
| Voltage colour                 | Black  |
| Duration                       | 7 h  |
| Material                       | Polycarbonate: cover   |
| Contacts material              | Screws: brass  |
| Connections - terminals        | Screw terminals 4...16 mm <sup>2</sup> rigid or stranded cable |
| Tightening torque              | 0.8 N.m  |
| Socket number                  | 1  |
| Socket-outlet type             | S  |
| Outlet standard                | Industrial   |
| Net weight                     | 0.293 kg   |
| Targeted country               | Australia  |

### Environment

|                                       |             |
|---------------------------------------|-------------|
| Ambient air temperature for operation | -25...75 °C |
| Standards                             | AS/NZS 3112 |

### Packing Units

|                              |         |
|------------------------------|---------|
| Unit Type of Package 1       | PCE     |
| Number of Units in Package 1 | 1       |
| Package 1 Weight             | 207.4 g |
| Package 1 Height             | 8 cm    |
| Package 1 width              | 9.5 cm  |
| Package 1 Length             | 9.7 cm  |

## Offer Sustainability

|                            |   |
|----------------------------|---|
| Sustainable offer status   | Green Premium product                         |
| REACH Regulation           | <a href="#">REACH Declaration</a>             |
| EU RoHS Directive          | Compliant <a href="#">EU RoHS Declaration</a> |
| Mercury free               | Yes   |
| RoHS exemption information | <a href="#">Yes</a>                           |
| China RoHS Regulation      | <a href="#">China RoHS Declaration</a>        |
| Environmental Disclosure   | <a href="#">Product Environmental Profile</a> |