

## Product data sheet

### Characteristics

# 56SO540-RO

## SOCKET OUTLET SURFACE 5 PIN ROUND

### 40A



#### Main

Range of product	Series 56
Product brand	Clipsal

#### Complementary

Device mounting	Surface
Mounting mode	External mounting
[In] rated current	40 A
[Ue] rated operational voltage	500 V 50/60 Hz conforming to EN 60309-2
Voltage colour	Black
Duration	7 h
Material	PVC (polyvinyl chloride)
Socket number	1
Socket-outlet type	T
Depth	102 mm
Width	101 mm
Height	107 mm

#### Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	10.2 cm
Package 1 Width	10.1 cm
Package 1 Length	10.7 cm
Package 1 Weight	0.6 kg

#### Offer Sustainability

REACH Regulation	<a href="#">REACH Declaration</a>
EU RoHS Directive	Compliant with Exemptions
China RoHS Regulation	<a href="#">China RoHS Declaration</a>
RoHS exemption information	<a href="#">Yes</a>