

Product data sheet

Characteristics

56SO610LE-GY

SOCKET OUTLET SURFACE 6 PIN ROUND

10A LESS ENCLOSURE



Main

Range of product	Series 56
Product brand	Clipsal





Complementary

Device mounting	Surface
Mounting mode	External mounting
[In] rated current	10 A
[Ue] rated operational voltage	500 V 50/60 Hz conforming to EN 60309-2
Voltage colour	Black
Duration	7 h
Material	PVC (polyvinyl chloride)
Socket number	1
Depth	39 mm
Width	101 mm
Height	101 mm

Packing Units

Package 1 Weight	0.001 kg
Package 1 Height	39.000 mm
Package 1 width	101.000 mm
Package 1 Length	101.000 mm

Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	 REACH Declaration
EU RoHS Directive	Compliant  EU RoHS Declaration
Mercury free	Yes
RoHS exemption information	 Yes
China RoHS Regulation	 China RoHS Declaration
Environmental Disclosure	 Product Environmental Profile