

Product data sheet

Characteristics

56SPO310-RW

56 Series Pendant Outlet - Switched - 3 Pin - 10A - 250V



Main

Range of product	Series 56
Range	Clipsal - 56 Series
Product brand	Clipsal
Product or component type	Pendant outlet
Device application	Power supply
Colour	White (RAL 9003)

Complementary

Number of poles	2
Plug, socket category	Low voltage
Plug, socket, control station shape	Straight
[In] rated current	10 A
[Ue] rated operational voltage	250 V AC 50 Hz conforming to EN 60309-2
Poles description	1P + N + E
Voltage colour	Blue
Duration	6 h
Material	PBT (polybutylene terephthalate): housing
Contacts material	Sleeves: brass
Connections - terminals	Screw terminals 0.75...2.5 mm ²
Connections - terminals	Screw terminal
Socket number	1
Outlet standard	Industrial
Cable outer diameter	7...10 mm
Cable entry	Cable gland
Thread type	M20
Net weight	0.26 kg
Depth	183 mm
Width	83 mm
Height	83 mm
Targeted country	Australia

Environment

IP degree of protection	IP66 conforming to AS 60529
Ambient air temperature for operation	-25...75 °C
Standards	AS/NZS 3120

Packing Units

Package 1 Weight	266 g
------------------	-------

Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	REACH Declaration
EU RoHS Directive	Compliant EU RoHS Declaration
Mercury free	Yes
RoHS exemption information	Yes
China RoHS Regulation	China RoHS Declaration
Environmental Disclosure	Product Environmental Profile