

## Product data sheet

### Characteristics

# 56SPO315-RW

Clipsal - 56 Series, Pendant Outlet, 250V, 15A,  
3 Flat PIN, 2 Pole



#### Main

Range of product	Series 56
Range	Clipsal - 56 Series
Product brand	Clipsal
Product or component type	Pendant outlet
Device application	Power supply
Colour	White (RAL 9003)

#### Complementary

Number of poles	2
Plug, socket category	Low voltage
Plug, socket, control station shape	Straight
[In] rated current	15 A
[Ue] rated operational voltage	250 V AC 50 Hz conforming to EN 60309-2
Poles description	1P + N + E
Voltage colour	Blue
Duration	6 h
Material	PBT (polybutylene terephthalate): housing
Contacts material	Sleeves: brass
Connections - terminals	Screw terminals 0.75...2.5 mm <sup>2</sup>
Connections - terminals	Screw terminal
Socket number	1
Outlet standard	Industrial
Cable outer diameter	7...10 mm
Cable entry	Cable gland
Thread type	M20
Net weight	0.26 kg
Depth	183 mm
Width	83 mm
Height	83 mm
Targeted country	Australia

#### Environment

IP degree of protection	IP66 conforming to AS 60529
Ambient air temperature for operation	-25...75 °C
Standards	AS/NZS 3120

## Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	7.8 cm
Package 1 Width	9.4 cm
Package 1 Length	17.6 cm
Package 1 Weight	260 g

## Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	<a href="#">REACH Declaration</a>
EU RoHS Directive	Compliant with Exemptions
China RoHS Regulation	<a href="#">China RoHS Declaration</a>
RoHS exemption information	<a href="#">Yes</a>
Environmental Disclosure	<a href="#">Product Environmental Profile</a>
Circularity Profile	No need of specific recycling operations